



## Main

|                                    |  |
|------------------------------------|--|
| Range of product                   | PrismaSeT G  |
| Range                              | PrismaSeT  |
| Range compatibility                | PrismaSeT PrismaSeT G enclosure                                      |
| Product or component type          | Gland plate  |
| Accessory / separate part category | Enclosure accessory  |
| Product compatibility              | IP30 enclosure<br>IP31 enclosure<br>IP55 enclosure<br>IP43 enclosure |

## Complementary

|                               |  |
|-------------------------------|--|
| Enclosure/cubicle description | Wall-mounted enclosure - width 600 mm<br>Floor-standing enclosure - width 600 mm<br>Wall-mounted duct - width 300 mm<br>Floor-standing duct - width 300 mm                                   |
| Type of gland plate           | Membrane   |
| Mounting location             | Top<br>Bottom  |
| Material                      | Insulated material   |
| Cable entry number            | 4 diameter: 7...14 mm<br>8 diameter: 3 mm<br>1 diameter: 17...30 mm<br>4 diameter: 3...7 mm<br>4 diameter: 5 mm<br>10 diameter: 7...12 mm<br>10 diameter: 7...10 mm<br>2 diameter: 7...18 mm |
| Quantity per set              | Set of 1   |
| Depth                         | 180 mm   |
| Net weight                    | 0.28 kg  |
| Colour                        | White (RAL 9003)   |

## Environment

|                         |      |
|-------------------------|------|
| IP degree of protection | IP55 |
|-------------------------|------|

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 3.000 cm  |
| Package 1 Width              | 8.300 cm  |
| Package 1 Length             | 21.700 cm |
| Package 1 Weight             | 279.000 g |
| Unit Type of Package 2       | S02       |
| Number of Units in Package 2 | 20        |
| Package 2 Height             | 15.000 cm |
| Package 2 Width              | 30.000 cm |

|                              |            |
|------------------------------|------------|
| Package 2 Length             | 40.000 cm  |
| Package 2 Weight             | 5.850 kg   |
| Unit Type of Package 3       | P12        |
| Number of Units in Package 3 | 240        |
| Package 3 Height             | 43.000 cm  |
| Package 3 Width              | 80.000 cm  |
| Package 3 Length             | 120.000 cm |
| Package 3 Weight             | 81.000 kg  |

### Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product  |
| REACH Regulation           | <a href="#">REACH Declaration</a>  |
| REACH free of SVHC         | Yes  |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes  |
| Mercury free               | Yes  |
| RoHS exemption information | <a href="#">Yes</a>  |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>   |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>  |
| Circularity Profile        | No need of specific recycling operations   |