



Main

Range	PowerLogic
Product or component type	Remote display
Device application	Human-machine dialogue application
Range compatibility	PowerLogic PowerLogic PM8000 PowerLogic PowerLogic ION7400
Display type	Colour TFT LCD

Complementary

Display resolution	320 x 240 pixels QVGA
Display size	3.5 inch
Information displayed	Energy consumption Voltage Power Harmonic distortion Frequency Current System alarm I/O status
Messages display capacity	Graphic objects (bargraph, button, light...)
Local signalling	Status: LED (green) Alarm: LED (red)
Control type	5 x push-button
Connector type	RJ45
Provided equipment	Mounting hardware Cable (with 3 m)
Mounting mode	Flush-mounted
Mounting support	Framework remote display
Width	96 mm
Height	96 mm
Projecting depth	27 mm
Net weight	300 g

Environment

IP degree of protection	IP54 conforming to IEC 60529
Relative humidity	5...95 %
Operating altitude	0...3000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C
Product certifications	IEC

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.97 cm
Package 1 Width	13.97 cm
Package 1 Length	19.05 cm
Package 1 Weight	0.52 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov