

### Main

Range of product	U.motion
Range compatibility	KNX
Product or component type	Touch panel
Device short name	Client Touch 7
Product destination	U.motion system
Device presentation	Complete device
Bus type	Ethernet
Operating system	Android
Display size	7 inch
Display colour	65000 colours
Colour tint	Aluminium

### Complementary

Connector type	1 RJ45 2 USB
Integrated connection type	Loudspeaker Microphone
Device mounting	Flush
[Ue] rated operational voltage	9...36 V DC
Maximum power consumption in W	7 W operation
Control type	Touch screen
Display type	TFT
Display resolution	800 x 480 pixels WSVGA
Illuminating intensity	500 cd
Memory type	512 MB RAM
Mounting position	Horizontal and vertical
Material	Plastic and metal
Height	136 mm
Width	215 mm
Depth	31 mm
Net weight	0.6 kg




### Environment

Ambient air temperature for operation	0...30 °C
IP degree of protection	IP20 conforming to EN 60529

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	22.2 cm
Package 1 Width	7.5 cm
Package 1 Length	27.5 cm
Package 1 Weight	1.3 kg

## Offer Sustainability

EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins