



## Main

Range	ClimaSys
Product	ClimaSys CA
Range compatibility	ClimaSys ClimaSys CV fan
Product or component type	Outlet grille
Accessory / separate part category	Thermal management accessory
Accessory / separate part destination	ClimaSys ventilation system
Fixing mode	Clipped By screws
Device composition	1 support frame 1 external part 1 G2 M1 synthetic standard filter

## Complementary

Material	Injected thermoplastic (ASA PC)
Colour	External part: grey (RAL 7035)
Cut-out dimensions	125 x 125 mm
Height	External: 170 mm
Width	External: 150 mm
Depth	External : 15 mm

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	15.500 cm
Package 1 Length	18.000 cm
Package 1 Weight	220.000 g
Unit Type of Package 2	CAR
Number of Units in Package 2	56
Package 2 Height	38.500 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	13.000 kg
Unit Type of Package 3	P12
Number of Units in Package 3	448
Package 3 Height	91.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	119.000 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------