



Main

Range	ClimaSys
Product name	ClimaSys CR
Product or component type	Resistance heater
Power range	90 W
Input voltage	12...24 V DC

Complementary

Operating position	Vertical
Ambient air temperature for operation	-40...70 °C
IP degree of protection	IP20
Product certifications	VDE[RETURN]UL
Material	Body: extruded aluminium
Condition of use	Heaters must be installed with a thermal controller Electrical protection is needed Air sealed enclosure
Fixing mode	By clips
Mounting support	35 mm DIN rail

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6 cm
Package 1 Width	8 cm
Package 1 Length	19.5 cm
Package 1 Weight	476 g
Unit Type of Package 2	PAL
Number of Units in Package 2	16
Package 2 Height	20 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	7.616 kg

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	RECh Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------