

Main

Range	PanelSeT
Product name	PanelSeT CRN
Application	Multi-purpose
Category	Compact enclosure
Enclosure nominal height	600 mm
Enclosure nominal width	400 mm
Enclosure nominal depth	200 mm
Installation accessory type	Wall-mounting
Device composition	1 body 1 cable gland plate 1 door 1 lock
Door type	Plain
Mounting plate description	Without mounting plate

Complementary

Body type	Sides made from a single folded section Back welded with double profile forming a protected sealed area
Number of doors	Front face: 1 door(s)
Door opening side	Reversible (120 °)
Lock type	3 mm double-bar lock
Type of gland plate	Standard
Accessibility for operation	Front
Removable parts	Door by hinges Cable gland plate by screws
Material	Body: steel
Surface finish	Epoxy-polyester powder
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product certifications	cUL[RETURN]UL[RETURN]DNV-GL
Net weight	9.83 kg

Environment

IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	61.000 cm
Package 1 Width	21.500 cm
Package 1 Length	41.000 cm
Package 1 Weight	9.636 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	30

Package 2 Height	196.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	302.000 kg

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
SCIP Number	E893f0a0-d2cc-4011-9425-3873dde70142
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Take-back	No

Contractual warranty

Warranty	18 months
----------	-----------