



## Main

Range	PanelSeT
Product name	PanelSeT CRN
Application	Multi-purpose
Category	Compact enclosure
Enclosure nominal height	800 mm
Enclosure nominal width	800 mm
Enclosure nominal depth	300 mm
Installation accessory type	Wall-mounting
Device composition	1 body 1 door 1 lock 2 cable gland plate: bottom
Door type	Plain
Mounting plate description	Without mounting plate

## Complementary

Body type	Sides made from a single folded section Back welded with double profile forming a protected sealed area
Number of doors	Front face: 1 door(s)
Door opening side	Reversible (120 °)
Lock type	3 mm double-bar lock
Type of gland plate	Standard
Accessibility for operation	Front
Removable parts	Door by hinges Cable gland plate by screws
Material	Body: steel
Surface finish	Epoxy-polyester powder
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product certifications	UL[RETURN]cUL[RETURN]DNV-GL
Net weight	29.034 kg

## Environment

IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	32.5 cm
Package 1 Width	81.0 cm
Package 1 Length	81.5 cm
Package 1 Weight	24.973 kg
Unit Type of Package 2	PAM

Number of Units in Package 2	8
Package 2 Height	176.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	212.784 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

### Contractual warranty

Warranty	18 months
----------	-----------