



Main

Range of product	Lighting and power sockets
Accessory / separate part category	Lighting accessory
Product or component type	Lamp
Device application	Multi-purpose
Device composition	1 lamp 1 fixing elements
Power factor	0.9

Complementary

Outlet standard deviation	Schuko
Rated lamp wattage	10 W
[Ue] rated operational voltage	230 V AC 50/60 Hz
Bulb base	Integral LED
Bulb type	LED
Control type	Built-in switch
Luminous flux	950 lm
Colour temperature	4000 K
Service life in hours	25000 h
Electrical connection	Cable quick connector 3 m not supplied Cable quick connector 1 m not supplied
Mounting support	Bracket DIN rail Metal parts
Fixing mode	Clip-in Magnetic fixing Screws
Range compatibility	Spacial Thalassa
Material	PC (UL94 V-0)
Length	372 mm
Height	63 mm
Width	40 mm
Colour	Black (RAL 9005)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

IP degree of protection	IP20 conforming to IEC 60529
Electrical insulation class	Class I
Electromagnetic compatibility	EMC immunity conforming to EN 55015
Standards	UL 1598 IEC 60598 EN 55015 UL 94 UL 8750 UL 508 A
Ambient air temperature for operation	-16...65 °C
Ambient air temperature for storage	-10...60 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.000 cm
Package 1 Width	7.500 cm
Package 1 Length	40.000 cm
Package 1 Weight	854.400 g
Unit Type of Package 2	S04
Number of Units in Package 2	10
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	9.544 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins