

Main

Range	PanelSeT
Accessory / separate part category	Mounting accessory
Product or component type	Mounting plate
Device application	Multi-purpose
Enclosure nominal dimensions	- H: 600 mm W: 500 mm H: 500 mm W: 600 mm
Mounting location	Direct fixing on backstuds Step slide
Mounting plate description	Plain
Range compatibility	PanelSeT PanelSeT S3D PanelSeT PanelSeT CRN Thalassa Thalassa PLM
Quantity per set	Set of 1
Material	Galvanised steel



Complementary

Fixing mode	Screwed on backstuds - screw type M8 By fixing element
Permanent permissible load	90 kg
Height	550 mm
Width	450 mm
Thickness	1.8 mm
Net weight	3.6 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.300 cm
Package 1 Width	45.000 cm
Package 1 Length	55.000 cm
Package 1 Weight	3.600 kg
Unit Type of Package 2	P12
Number of Units in Package 2	75
Package 2 Height	37.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	291.500 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Take-back	No

Contractual warranty

Warranty	18 months
----------	-----------