



Main

Range	PanelSeT
Accessory / separate part category	Mounting accessory
Product or component type	Mounting plate
Device application	Multi-purpose
Enclosure nominal dimensions	- H: 800 mm W: 800 mm
Mounting location	Direct fixing on backstuds Step slide
Mounting plate description	Plain
Range compatibility	PanelSeT PanelSeT S3D PanelSeT PanelSeT CRN Thalassa Thalassa PLM
Quantity per set	Set of 1
Material	Galvanised steel

Complementary

Fixing mode	Screwed on backstuds - screw type M8 By fixing element
Permanent permissible load	150 kg
Height	750 mm
Width	750 mm
Thickness	2.5 mm
Net weight	11.05 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.8 cm
Package 1 Width	75.7 cm
Package 1 Length	76.5 cm
Package 1 Weight	11.15 kg
Unit Type of Package 2	P12
Number of Units in Package 2	45
Package 2 Height	120 cm
Package 2 Width	80 cm
Package 2 Length	34 cm
Package 2 Weight	514 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------