

NSYMP168

Plain mounting plate, PanelSeT SFN, PanelSeT SF, PanelSeT SM, for electrical enclosure H1600 W800mm, galvanized steel



Main

Range	PanelSeT
Accessory / separate part category	Mounting accessory
Product or component type	Mounting plate
Device application	Multi-purpose
Enclosure nominal dimensions	- H: 1600 mm W: 800 mm
Mounting plate description	Plain
Range compatibility	PanelSeT PanelSeT SF PanelSeT PanelSeT SM PanelSeT PanelSeT SFX PanelSeT PanelSeT SMX
Device composition	1 mounting plate 2 sliding shoes
Quantity per set	Set of 1
Material	Galvanised steel

Complementary

Fixing mode	By fixing brackets
Maximum load	300 kg/m ²
Permanent permissible load	500 Kg intermediate position 600 kg back of the enclosure
Height	Fixing centers: 1450 mm Nominal: 1600 mm Real: 1497 mm
Width	Nominal: 800 mm Fixing centers: 650 mm Real: 696 mm
Depth	27 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.500 cm
Package 1 Width	70.000 cm
Package 1 Length	150.000 cm
Package 1 Weight	25.500 kg
Unit Type of Package 2	P2M
Number of Units in Package 2	20
Package 2 Height	80.000 cm
Package 2 Width	120.000 cm
Package 2 Length	200.000 cm
Package 2 Weight	540.000 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------