

# NSYMP1810

Plain mounting plate, PanelSeT SFN, PanelSeT SF, PanelSeT SM, for electrical enclosure H1800 W1000mm, galvanized steel



## Main

Range	PanelSeT
Accessory / separate part category	Mounting accessory
Product or component type	Mounting plate
Device application	Multi-purpose
Enclosure nominal dimensions	-
Mounting plate description	Plain
Range compatibility	PanelSeT PanelSeT SF PanelSeT PanelSeT SM PanelSeT PanelSeT SFX PanelSeT PanelSeT SMX
Device composition	1 mounting plate 2 sliding shoes
Quantity per set	Set of 1
Material	Galvanised steel

## Complementary

Fixing mode	By fixing brackets
Maximum load	300 kg/m <sup>2</sup>
Permanent permissible load	500 Kg intermediate position 600 kg back of the enclosure
Height	Fixing centers: 1650 mm Nominal: 1800 mm Real: 1697 mm
Width	Fixing centers: 850 mm Nominal: 1000 mm Real: 896 mm
Depth	27 mm

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	90 cm
Package 1 Length	171 cm
Package 1 Weight	34.2 kg
Unit Type of Package 2	P2M
Number of Units in Package 2	20
Package 2 Height	80 cm
Package 2 Width	200 cm
Package 2 Length	120 cm
Package 2 Weight	720 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------