

# NSYS3D121030

Wall mounted steel enclosure, Spacial S3D, plain door, without mounting plate, 1200x1000x300mm, IP66, IK10



## Main

|                             |   |
|-----------------------------|---|
| Range                       | Spacial   |
| Product name                | Spacial S3D                                       |
| Application                 | Multi-purpose                                     |
| Category                    | Compact enclosure                                 |
| Enclosure nominal height    | 1200 mm   |
| Enclosure nominal width     | 1000 mm   |
| Enclosure nominal depth     | 300 mm  |
| Door type                   | Plain   |
| Mounting plate description  | Without mounting plate                            |
| Type of gland plate         | Standard  |
| Installation accessory type | Wall-mounting                                     |
| Device composition          | 1 body<br>2 cable gland plate<br>1 door<br>1 lock |

## Complementary

|                             |  |
|-----------------------------|--|
| Body type                   | Single piece body<br>Gutter-shaped front rail double sheet thickness |
| Number of doors             | Front face: 1 door(s)  |
| Door opening side           | Reversible (120 °)   |
| Lock type                   | 3 points lock, 3 mm double-bar                                       |
| Accessibility for operation | Front  |
| Removable parts             | Door by hinges<br>Cable gland plate by screws                        |
| Material                    | Steel  |
| Surface finish              | Epoxy-polyester powder   |
| Colour                      | Grey (RAL 7035)  |
| Standards                   | IEC 62208  |
| Product certifications      | BV[RETURN]GL[RETURN]cUL[RETURN]LR[RETURN]DNV[RETURN]UL               |
| Net weight                  | 53 kg  |

## Environment

|                           |                              |
|---------------------------|------------------------------|
| NEMA degree of protection | NEMA 4X/13                   |
| IK degree of protection   | IK10 conforming to IEC 62262 |
| IP degree of protection   | IP66 conforming to IEC 60529 |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 34.5 cm   |
| Package 1 Width              | 108.0 cm  |
| Package 1 Length             | 122.0 cm  |
| Package 1 Weight             | 48.731 kg |
| Unit Type of Package 2       | P12       |
| Number of Units in Package 2 | 2         |
| Package 2 Height             | 122 cm    |
| Package 2 Width              | 80 cm     |
| Package 2 Length             | 115 cm    |
| Package 2 Weight             | 114 kg    |

## Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product                                      |
| REACH Regulation           | <a href="#">REACH Declaration</a>                          |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) |
| Mercury free               | Yes  |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                     |
| RoHS exemption information | <a href="#">Yes</a>  |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>              |
| Circularity Profile        | No need of specific recycling operations                   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|