



Main

| | |
|-----------------------------|---|
| Range | PanelSeT |
| Product name | PanelSeT SM |
| Product or component type | Compact enclosure |
| Application | Multi-purpose |
| Installation accessory type | Floor-standing |
| Device composition | 1 body 2 door 2 cable gland plate 1 locking system with handle: door 1 blocking system: left door 4 mounting plate bracket |
| Removable parts | Door by screws hinge Mounting plate bracket by screws |
| Enclosure nominal height | 1400 mm |
| Enclosure nominal width | 1200 mm |
| Enclosure nominal depth | 400 mm |

Complementary

| | |
|-----------------------------|--|
| Number of doors | Front: 2 door(s) |
| Door opening side | Left (120 °) Right (120 °) |
| Door type | Plain |
| Lock type | 4 points lock, handle with 5 mm double bar insert |
| Body type | Single piece body with welded rear panel Front part forming a rigid frame with welded corners |
| Mounting plate description | Without mounting plate |
| Type of gland plate | Standard |
| Cable entry | 1 entry |
| Material | Body: sheet steel Door: sheet steel Hinge: zamak |
| Surface finish | Epoxy-polyester powder |
| Colour | Enclosure: grey (RAL 7035) Handle: black (RAL 9005) |
| Accessibility for operation | Front |
| Net weight | 81 kg |

Environment

| | |
|-------------------------|------------------------------|
| Standards | IEC 62208 |
| Product certifications | DNV[RETURN]UL[RETURN]BV |
| IK degree of protection | IK10 conforming to IEC 62262 |
| IP degree of protection | IP55 conforming to IEC 60529 |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 153.0 cm |
| Package 1 Width | 124.5 cm |
| Package 1 Length | 49.0 cm |
| Package 1 Weight | 81.0 kg |
| Unit Type of Package 2 | PAL |
| Number of Units in Package 2 | 2 |
| Package 2 Height | 98 cm |
| Package 2 Width | 125 cm |
| Package 2 Length | 153 cm |
| Package 2 Weight | 189 kg |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|