



### Main

|                             |   |
|-----------------------------|---|
| Range                       | PanelSeT  |
| Product name                | PanelSeT SM   |
| Product or component type   | Compact enclosure   |
| Application                 | Multi-purpose   |
| Installation accessory type | Floor-standing  |
| Device composition          | 1 body<br>1 cable gland plate<br>1 locking system with handle: door<br>4 mounting plate bracket<br>1 mounting plate<br>1 door |
| Removable parts             | Door by screws hinge<br>Mounting plate by screws mounting plate bracket<br>Mounting plate bracket by screws                   |
| Enclosure nominal height    | 1400 mm   |
| Enclosure nominal width     | 800 mm  |
| Enclosure nominal depth     | 300 mm  |

### Complementary

|                             |  |
|-----------------------------|--|
| Number of doors             | Front: 1 door(s)   |
| Door opening side           | Reversible (120 °)   |
| Door type                   | Plain  |
| Lock type                   | 4 points lock, handle with 5 mm double bar insert  |
| Body type                   | Front part forming a rigid frame with welded corners<br>Single piece body with welded rear panel |
| Mounting plate description  | Plain  |
| Type of gland plate         | Standard   |
| Cable entry                 | 1 entry  |
| Material                    | Mounting plate: galvanised steel<br>Body: sheet steel<br>Door: sheet steel<br>Hinge: zamak       |
| Surface finish              | Epoxy-polyester powder   |
| Colour                      | Enclosure: grey (RAL 7035)<br>Handle: black (RAL 9005)   |
| Accessibility for operation | Front  |
| Net weight                  | 73 kg  |

### Environment

|                         |                              |
|-------------------------|------------------------------|
| Standards               | IEC 62208                    |
| Product certifications  | UL[RETURN]DNV[RETURN]BV      |
| IK degree of protection | IK10 conforming to IEC 62262 |
| IP degree of protection | IP55 conforming to IEC 60529 |

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Height             | 153.0 cm |
| Package 1 Width              | 84.5 cm  |
| Package 1 Length             | 39.0 cm  |
| Package 1 Weight             | 73.0 kg  |
| Unit Type of Package 2       | PAL      |
| Number of Units in Package 2 | 2        |
| Package 2 Height             | 78 cm    |
| Package 2 Width              | 85 cm    |
| Package 2 Length             | 153 cm   |
| Package 2 Weight             | 167 kg   |

## Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product                                      |
| REACH Regulation           | <a href="#">REACH Declaration</a>                          |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) |
| Mercury free               | Yes  |
| RoHS exemption information | <a href="#">Yes</a>  |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                     |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>              |
| Circularity Profile        | No need of specific recycling operations                   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|