

Main

Range	PanelSeT
Product name	PanelSeT SM
Product or component type	Compact enclosure
Application	Multi-purpose
Installation accessory type	Floor-standing
Device composition	1 body 2 door 1 cable gland plate 1 locking system with handle: door 1 blocking system: left door 4 mounting plate bracket 1 mounting plate
Removable parts	Door by screws hinge Mounting plate by screws mounting plate bracket Mounting plate bracket by screws
Enclosure nominal height	1600 mm
Enclosure nominal width	1000 mm
Enclosure nominal depth	300 mm

Complementary

Number of doors	Front: 2 door(s)
Door opening side	Left (120 °) Right (120 °)
Door type	Plain
Lock type	4 points lock, handle with 5 mm double bar insert
Body type	Front part forming a rigid frame with welded corners Single piece body with welded rear panel
Mounting plate description	Plain
Type of gland plate	Standard
Cable entry	1 entry
Material	Mounting plate: galvanised steel Body: sheet steel Door: sheet steel Hinge: zamak
Surface finish	Epoxy-polyester powder
Colour	Enclosure: grey (RAL 7035) Handle: black (RAL 9005)
Accessibility for operation	Front
Net weight	113 kg

Environment

Standards	IEC 62208
Product certifications	UL[RETURN]BV[RETURN]DNV
IK degree of protection	IK10 conforming to IEC 62262
IP degree of protection	IP55 conforming to IEC 60529

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	173.000 cm
Package 1 Width	105.000 cm
Package 1 Length	39.000 cm
Package 1 Weight	115.000 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	2
Package 2 Height	173.000 cm
Package 2 Width	105.000 cm
Package 2 Length	78.000 cm
Package 2 Weight	230.000 kg

Offer Sustainability

SCIP Number	52da316e-d4e1-4114-85c0-32a03b2934fd
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	803

Contractual warranty

Warranty	18 months
----------	-----------