



### Main

Range	PanelSeT
Product name	PanelSeT SM
Product or component type	Compact enclosure
Application	Multi-purpose
Installation accessory type	Floor-standing
Device composition	1 body 2 door 2 cable gland plate 1 locking system with handle: door 1 blocking system: left door 4 mounting plate bracket 1 mounting plate
Removable parts	Door by screws hinge Mounting plate by screws mounting plate bracket Mounting plate bracket by screws
Enclosure nominal height	2000 mm
Enclosure nominal width	1200 mm
Enclosure nominal depth	600 mm

### Complementary

Number of doors	Front: 2 door(s)
Door opening side	Left (120 °) Right (120 °)
Door type	Plain
Lock type	4 points lock, handle with 5 mm double bar insert
Body type	Front part forming a rigid frame with welded corners Single piece body with welded rear panel
Mounting plate description	Plain
Type of gland plate	Standard
Cable entry	1 entry
Material	Mounting plate: galvanised steel Body: sheet steel Door: sheet steel Hinge: zamak
Surface finish	Epoxy-polyester powder
Colour	Enclosure: grey (RAL 7035) Handle: black (RAL 9005)
Accessibility for operation	Front
Net weight	200 kg

### Environment

Standards	IEC 62208
Product certifications	BV[RETURN]DNV[RETURN]JUL
IK degree of protection	IK10 conforming to IEC 62262
IP degree of protection	IP55 conforming to IEC 60529

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	213.0 cm
Package 1 Width	124.5 cm
Package 1 Length	69.0 cm
Package 1 Weight	200.0 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------