



### Main

Range	Spacial
Product name	Spacial SM
Product or component type	Compact enclosure
Application	Multi-purpose
Installation accessory type	Floor-standing
Device composition	1 body 1 cable gland plate 1 locking system with handle: door 4 mounting plate bracket 1 door
Removable parts	Door by screws hinge Mounting plate bracket by screws
Enclosure nominal height	2000 mm
Enclosure nominal width	800 mm
Enclosure nominal depth	500 mm

### Complementary

Number of doors	Front: 1 door(s)
Door opening side	Reversible (120 °)
Door type	Plain
Lock type	4 points lock, handle with 5 mm double bar insert
Body type	Front part forming a rigid frame with welded corners Single piece body with welded rear panel
Mounting plate description	Without mounting plate
Type of gland plate	Standard
Cable entry	1 entry
Material	Body: sheet steel Door: sheet steel Hinge: zamak
Surface finish	Epoxy-polyester powder
Colour	Enclosure: grey (RAL 7035) Handle: black (RAL 9005)
Accessibility for operation	Front
Net weight	102 kg

### Environment

Standards	IEC 62208
Product certifications	BV[RETURN]DNV[RETURN]JUL
IK degree of protection	IK10 conforming to IEC 62262
IP degree of protection	IP55 conforming to IEC 60529

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	213.0 cm
Package 1 Width	84.5 cm
Package 1 Length	59.0 cm
Package 1 Weight	102.0 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------