



Main

Range	PanelSeT
Product name	PanelSeT SMX
Enclosure type	Multi-purpose
Category	Compact enclosure
Nominal height	2000 mm
Nominal width	1200 mm
Nominal depth	500 mm
Product installation	Floor-standing
Device composition	1 body 2 door 1 cable gland plate 1 locking system with handle: door 4 mounting plate bracket

Complementary

Body type	Single piece body folded and welded
Door type	Plain
Door opening side	Reversible (120 °)
Number of doors	Front face: 2 door(s)
Lock type	3 points lock, handle with 5 mm double-bar insert
Type of gland plate	Plain
Accessibility for operation	Front
Mounting plate description	Without mounting plate
Material	Body and door: stainless steel 304L Handle: zamak Hinge: stainless steel
Removable parts	Door by hinges Mounting plate bracket by screws Cable gland plate by clips
Surface finish	Enclosure: Scotch-Brite® brushed Handle: painted
Net weight	180 kg

Environment

Standards	IEC 62208
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Product certifications	CAN/CSA 22[RETURN]JUL 508
Environmental characteristic	Corrosive Specific hygiene

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	213.000 cm
Package 1 Width	125.000 cm
Package 1 Length	59.000 cm
Package 1 Weight	137.000 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------