



Main

Range	Thalassa
Product or component type	Door switch
Application	Multi-purpose
Nominal dimensions of the housing	-
Mounting location	Enclosure
Range compatibility	Thalassa PLA enclosure
Device composition	Fixing elements 1 x switch/commutator unit 1 x fixing support

Complementary

Fixing mode	Direct fixing - enclosure location
Input type	NC + NO
Absolute maximum input	3 A/240 V

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	5.000 cm
Package 1 Length	13.000 cm
Package 1 Weight	233.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	40
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	9.780 kg
Unit Type of Package 3	P12
Number of Units in Package 3	320
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	91.040 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Environmental Disclosure

 [Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations

Contractual warranty

Warranty

18 months
