

Product data sheet

Characteristics

NSYTRAC162

Cover plate, Linergy TR, 2 points, 2.2mm width, for screw terminal NSYTRV162, grey, Set of 50



Main

| | |
|------------------------------------|---|
| Range | Linergy |
| Product name | Linergy TR |
| Product or component type | Cover plate |
| Device short name | TRA |
| Accessory / separate part category | Insulation accessory |
| Product compatibility | TRV screw terminal - passthrough terminal block, length = 55.5 mm TRV screw terminal - protective earth terminal block, length = 55.5 mm |
| Thickness | 2.2 mm |

Complementary

| | |
|-----------------------------|--------------------|
| Cable cross section | 16 mm ² |
| Number of connections | 2 |
| Number of measurement input | 2 |
| Quantity per set | Set of 50 |
| Net weight | 3.5 g |
| Colour | Grey |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 0.500 cm |
| Package 1 Width | 5.000 cm |
| Package 1 Length | 5.500 cm |
| Package 1 Weight | 3.000 g |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 50 |
| Package 2 Height | 4.000 cm |
| Package 2 Width | 17.000 cm |
| Package 2 Length | 17.000 cm |
| Package 2 Weight | 179.000 g |
| Unit Type of Package 3 | S03 |
| Number of Units in Package 3 | 1600 |
| Package 3 Height | 30.000 cm |
| Package 3 Width | 30.000 cm |
| Package 3 Length | 40.000 cm |
| Package 3 Weight | 6.224 kg |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

| | |
|-----------------------------|--|
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Halogen content performance | Halogen free plastic parts product |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|