

Product data sheet

Characteristics

NSYTRACR62

Cover plate, Lineryg TR, 2 points, 2.2mm width, for spring terminals NSYTRR62, grey, Set of 50



Main

Range	Lineryg
Product name	Lineryg TR
Product or component type	Cover plate
Device short name	TRA
Accessory / separate part categor	Insulation accessory
Product compatibility	TRR spring terminal terminal block, length = 69.5 mm
Thickness	2.2 mm

Complementary

Cable cross section	6 mm ²
Number of connections	2
Number of measurement input	2
Quantity per set	Set of 50
Net weight	3.2 g
Colour	Grey

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	20.000 cm
Package 1 Length	24.000 cm
Package 1 Weight	3.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Height	4.000 cm
Package 2 Width	20.000 cm
Package 2 Length	24.000 cm
Package 2 Weight	173.000 g
Unit Type of Package 3	S04
Number of Units in Package 3	2400
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	9.324 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------