



### Main

Range of product	AccuSine
Product name	AccuSine PCS+
Product or component type	Active harmonic filter

### Complementary

Network type	3P
Network configuration	3 or 4 wires
Network rated voltage	380...480 V AC
Network frequency	50/60 Hz +/- 3 Hz auto sensing
Maximum permissible voltage	1.1 x Un
Neutral correction	Not provided
RMS output current rating	120 A
Reactive power rating	100 kvar 480 V AC 50/60 Hz
Operating modes	Power factor correction Harmonic cancellation Mains current balancing
Installation location	Indoor
Enclosure mounting	Wall mounted
Protection type	Without protection
Heat dissipation	Rear plenum with forced ventilation for high heat flow
Electromagnetic compatibility	Conducted EMC, class A conforming to EN 61000-6-4
Accessibility for operation	Front
Location of connection	Bottom

### Environment

Enclosure degree of protection	IP00
Environmental characteristic	Operating: 3C2 conforming to IEC 60721-3-3 Operating: 3S2 conforming to IEC 60721-3-3 Storage: 3C3 conforming to IEC 60721-3-3 Storage: 3S3 conforming to IEC 60721-3-3
Operating altitude	<= 1000 m 1 % per 100 m
Ambient air temperature for operation	0...40 °C 0...50 °C maximum with current derating of 2 % per °C
Relative humidity	0...95 %
PCBA protection	Conformal coated
Standards	EN 61000-6-4 UL 508 CSA C22.2 No 14 CSA C22.2 No 60947-1-07 UL 60947-1 EN 60439-1
Product certifications	CE[RETURN]cULus[RETURN]DNV-GL[RETURN]RCM[RETURN]ABS
Ambient air temperature for storage	-20...60 °C

Net weight	110 kg
Height	1400 mm
Width	421 mm
Colour	Light grey (RAL 7035)
Depth	384 mm

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	71.500 cm
Package 1 Width	73.500 cm
Package 1 Length	174.000 cm
Package 1 Weight	167.000 kg

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

## Contractual warranty

Warranty	18 months
----------	-----------