



### Main

|                           |                |
|---------------------------|----------------|
| Range                     | PratiKa        |
| Product or component type | Socket         |
| Device short name         | PratiKa socket |
| Plug, socket category     | Low voltage    |
| Poles description         | 3P + E         |
| Network type              | AC             |
| Outlet standard           | Industrial     |

### Complementary

|                                     |   |
|-------------------------------------|---|
| Mounting mode                       | Panel-mounted                                   |
| Plug, socket, control station shape | Angled  |
| [In] rated current                  | 32 A  |
| [Ue] rated operational voltage      | 100...130 V                                     |
| Network frequency                   | 50/60 Hz  |
| Ground lug clockwise position       | 4 h   |
| Plug, socket material               | Housing: self-extinguishing engineering polymer |
| Contacts material                   | Sleeves: brass                                  |
| Connections - terminals             | Fast connection                                 |
| Cable cross section                 | 2.5...6 mm <sup>2</sup>                         |
| Net weight                          | 0.256 kg  |
| Base dimension                      | 90 x 100 mm                                     |
| Height                              | 100 mm  |
| Width                               | 95 mm   |
| Depth                               | 118 mm  |
| Colour                              | Grey (RAL 7035)                                 |
| Voltage colour                      | Yellow  |

### Environment

|                                       |   |
|---------------------------------------|---|
| Standards                             | IEC 60309-2<br>IEC 60309-1                      |
| IP degree of protection               | IP67 conforming to IEC 60529                    |
| IK degree of protection               | IK08 conforming to EN 62262                     |
| Fire resistance                       | 850 °C conforming to IEC 60695-2-1              |
| Relative humidity                     | 50 % at 40 °C<br>70 % at 30 °C<br>90 % at 20 °C |
| Ambient air temperature for operation | 35 °C ( 86400 s )                               |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | PCE     |
| Number of Units in Package 1 | 1       |
| Package 1 Height             | 10.0 cm |
| Package 1 Width              | 9.0 cm  |
| Package 1 Length             | 7.0 cm  |
| Package 1 Weight             | 273.0 g |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| REACH Regulation           | <a href="#">REACH Declaration</a>   |
| EU RoHS Directive          | Compliant with Exemptions   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>  |
| Circularity Profile        | No need of specific recycling operations  |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|