



### Main

Range	Actassi
Product	19" patchcord guiding panel
Colour	Light grey (RAL 7035) Dark grey (RAL 7016)
Provided equipment	2 quick fix 19" mountings 4 openable rings

### Complementary

Rack unit	2U
Material	Metal sheet: DC01 1.2 mm Plastic part: PA66 GF20 Plastic part: PC
Width	484 Mm 0.48 m
Height	0.089 M 89 mm
Depth	100 Mm 0.100 m
Net weight	0.7000 Kg 0.7 kg

### Environment

Ambient air temperature for operation	-10...55 °C 14...131 °F
Standards	IEC 60297 NF C 20-150

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.0 cm
Package 1 Width	11.0 cm
Package 1 Length	51.5 cm
Package 1 Weight	849.0 g
Unit Type of Package 2	S04
Number of Units in Package 2	6
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	5.467 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

## Contractual warranty

Warranty	18 months
----------	-----------