



## Main

Network rated voltage	400 V AC 60 Hz 415 V AC 60 Hz
Reactive power rating	225 kvar
Operating mode	Automatic
Range	PowerLogic
Device short name	automatic capacitor bank
Product or component type	Capacitor bank

## Complementary

Tuning factor	2.7
Tuning frequency	162 Hz
Power per step	25 kvar
Step composition	25 + 2x50 + 100
Location of connection	Top
Poles description	3P
Main incomer protection	Without protection
[I <sub>cw</sub> ] rated short-time withstand current	50 kA (I <sub>cw</sub> )
Control type	Rotary handle

## Environment

Product certifications	IEC
Mounting location	Indoor

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	210.0 cm
Package 1 Width	80.0 cm
Package 1 Length	120.0 cm
Package 1 Weight	400.0 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>