



Main

Network rated voltage	400 V AC 60 Hz 415 V AC 60 Hz
Reactive power rating	275 kvar
Operating mode	Automatic
Range	PowerLogic
Device short name	automatic capacitor bank
Product or component type	Capacitor bank

Complementary

Tuning factor	2.7
Tuning frequency	162 Hz
Power per step	25 kvar
Step composition	25 + 50 + 2x100
Location of connection	Top
Poles description	3P
Main incomer protection	Without protection
[I _{cw}] rated short-time withstand current	50 kA (I _{cw})
Control type	Rotary handle

Environment

Product certifications	IEC
Mounting location	Indoor

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	210.0 cm
Package 1 Width	80.0 cm
Package 1 Length	120.0 cm
Package 1 Weight	400.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile