



Main

Network rated voltage	400 V AC 60 Hz 415 V AC 60 Hz
Reactive power rating	350 kvar
Operating mode	Automatic
Range	PowerLogic
Device short name	automatic capacitor bank
Product or component type	Capacitor bank

Complementary

Tuning factor	2.7
Tuning frequency	162 Hz
Power per step	50 kvar
Step composition	50 + 3x100
Location of connection	Top
Poles description	3P
Main incomer protection	Circuit breaker protection
Breaking capacity	Icc 65 kA
Control type	Rotary handle

Environment

Product certifications	IEC
Mounting location	Indoor

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	230.0 cm
Package 1 Width	80.0 cm
Package 1 Length	120.0 cm
Package 1 Weight	450.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

