



## Main

Network rated voltage	400 V AC 60 Hz 415 V AC 60 Hz
Reactive power rating	550 kvar
Operating mode	Automatic
Range	PowerLogic
Device short name	automatic capacitor bank
Product or component type	Capacitor bank

## Complementary

Tuning factor	3.8
Tuning frequency	228 Hz
Power per step	50 kvar
Step composition	50 + 5x100
Location of connection	Top
Poles description	3P
Main incomer protection	Without protection
[Icw] rated short-time withstand current	65 kA (Icw)
Control type	Rotary handle

## Environment

Product certifications	IEC
Mounting location	Indoor

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	230.0 cm
Package 1 Width	80.0 cm
Package 1 Length	156.0 cm
Package 1 Weight	950.0 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>