



Main

Range	Prisma
Range of product	Prisma G
Product or component type	Rail
Accessory / separate part category	Installation accessory
Range compatibility	Prisma (Prisma G)
Type of rail	Modular Adjustable
Installed device	TeSys: fixed GV2L TeSys: fixed GV2P TeSys: fixed GV3 ComPact: fixed NG160 without earth leakage protection - control: toggle ComPact: fixed NG160 NA without earth leakage protection - control: toggle ComPact: fixed NG160 with earth leakage protection - control: toggle ComPact: fixed NSXm without earth leakage protection - control: toggle - vertical installation ComPact: fixed NSXm with earth leakage protection - control: toggle - vertical installation
Poles description	9 x 3P: fixed GV2L 9 x 3P: fixed GV2P 7 x 3P: fixed GV3 1 x 3P: fixed NG160 1 x 4P: fixed NG160 1 x 3P: fixed NG160 NA 1 x 4P: fixed NG160 NA 1 x 3P or 4P: fixed NSXm vertical installation

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Complementary

Installation description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm
Number of vertical modules [50 mm]	3 module(s): GV2L, direct in 600 mm Widefloor-standing enclosure 3 module(s): GV2L, direct in 600 mm Widewall-mounted enclosure 3 module(s): GV2P, direct in 600 mm Widefloor-standing enclosure 3 module(s): GV2P, direct in 600 mm Widewall-mounted enclosure 5 module(s): GV3, direct in 600 mm Widefloor-standing enclosure 5 module(s): GV3, direct in 600 mm Widewall-mounted enclosure 5 module(s): NG160 without earth leakage protection , direct in 600 mm Widefloor-standing enclosure 5 module(s): NG160 without earth leakage protection , direct in 600 mm Widewall-mounted enclosure 5 module(s): NG160 NA without earth leakage protection , direct in 600 mm Widefloor-standing enclosure 5 module(s): NG160 NA without earth leakage protection , direct in 600 mm Widewall-mounted enclosure 7 module(s): NSXm without earth leakage protection , direct in 600 mm Widefloor-standing enclosure 7 module(s): NSXm without earth leakage protection , direct in 600 mm Widewall-mounted enclosure 7 module(s): NSXm without earth leakage protection , connection block in 600 mm Widefloor-standing enclosure 7 module(s): NSXm without earth leakage protection , connection block in 600 mm Widewall-mounted enclosure 5 module(s): NG160 with earth leakage protection , direct in 600 mm Widefloor-standing enclosure 5 module(s): NG160 with earth leakage protection , direct in 600 mm Widewall-mounted enclosure 7 module(s): NSXm with earth leakage protection , direct in 600 mm Widefloor-standing enclosure 7 module(s): NSXm with earth leakage protection , direct in 600 mm Widewall-mounted enclosure 7 module(s): NSXm with earth leakage protection , connection block in 600 mm Widefloor-standing enclosure 7 module(s): NSXm with earth leakage protection , connection block in 600 mm Widewall-mounted enclosure
9 mm pitches	48
Quantity per set	Set of 1
Height	58 mm
Width	467 mm
Depth	97 mm
Net weight	0.34 kg
Colour	Natural
Material	Metal

Environment

Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.8 cm
Package 1 Width	10.5 cm
Package 1 Length	46.8 cm
Package 1 Weight	330 g

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins