



### Main

Range	Prisma
Range of product	Prisma G Prisma P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	Prisma (Prisma G) duct Prisma (Prisma P) cubicle
Type of front plate	Plain
Installed device	TeSys: fixed TeSys U - horizontal installation Altistart: ATS01N103/106FT Phaseo: LV/LV transformer
Poles description	4 x 3P: modular rail support: TeSys U horizontal installation

### Complementary

Enclosure/cubicle description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Cubicle duct - width 400 mm depth 400 mm
Number of vertical modules [50 mm]	4
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA
Material	Steel
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	200 mm
Width	250 mm
Net weight	0.48 kg
Quantity per set	Set of 1
Functional unit	300 mm Prisma G floor-standing duct TeSys TeSys U fixed horizontal 3P 4 direct 4 300 mm Prisma G wall-mounted duct TeSys TeSys U fixed horizontal 3P 4 direct 4 300 mm Prisma G floor-standing duct Altistart ATS01N103/106FT 19 4 300 mm Prisma G wall-mounted duct Altistart ATS01N103/106FT 19 4 300 mm Prisma G floor-standing duct Phaseo LV/LV transformer 4 300 mm Prisma G wall-mounted duct Phaseo LV/LV transformer 4 400 mm 400 mm Prisma P cubicle 4

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	21.5 cm
Package 1 Length	26.5 cm
Package 1 Weight	470.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	16.5 cm

Package 2 Width	23.0 cm
Package 2 Length	27.5 cm
Package 2 Weight	4.9 kg
Unit Type of Package 3	P12
Number of Units in Package 3	600
Package 3 Height	113.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	283.2 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Halogen content performance	Halogen free plastic parts product