



### Main

Range	Prisma
Range of product	Prisma G
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	Prisma (Prisma G) enclosure
Type of front plate	Plain
Type of front plate	Plain

### Complementary

Enclosure/cubicle description	Floor-standing enclosure - width 850 mm
Number of vertical modules [50 mm]	4
Standards	IEC 61439-1 IEC 61439-2
Product certifications	ASEFA
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	200 mm
Width	750 mm
Net weight	1.46 kg
Quantity per set	Set of 1
Functional unit	850 mm Prisma G floor-standing enclosure

### Environment

IP degree of protection	IP30
-------------------------	------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	20 cm
Package 1 Length	75 cm
Package 1 Weight	1.46 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	6
Package 2 Height	10 cm
Package 2 Width	22 cm
Package 2 Length	76 cm
Package 2 Weight	9.1 kg
Unit Type of Package 3	P12
Number of Units in Package 3	60
Package 3 Height	33 cm
Package 3 Width	80 cm

Package 3 Length	120 cm
Package 3 Weight	99 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Halogen content performance	Halogen free plastic parts product