



Main

Range	Prisma
Range of product	Prisma G
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	Prisma (Prisma G) enclosure
Type of front plate	Plain
Type of front plate	Plain

Complementary

Enclosure/cubicle description	Floor-standing enclosure - width 850 mm
Number of vertical modules [50 mm]	6
Standards	IEC 61439-1 IEC 61439-2
Product certifications	ASEFA
Material	Steel
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	300 mm
Width	750 mm
Net weight	2.04 kg
Quantity per set	Set of 1
Functional unit	850 mm Prisma G floor-standing enclosure

Environment

IP degree of protection	IP30
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	30 cm
Package 1 Length	75 cm
Package 1 Weight	2.3 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	4
Package 2 Height	7 cm
Package 2 Width	32 cm
Package 2 Length	78 cm
Package 2 Weight	8.8 kg
Unit Type of Package 3	P12
Number of Units in Package 3	20
Package 3 Height	27 cm

Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	58 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Halogen content performance	Halogen free plastic parts product