



### Main

Range	Linergy
Range of product	Linergy
Product or component type	Multi-stage distribution block
Product name	Linergy BS
Range compatibility	Prisma Prisma G enclosure Prisma Prisma P enclosure
Product compatibility	Spacial enclosures
IP degree of protection	IPxx B

### Complementary

Mounting support	Slotted backplate Prisma upright Plain backplate
Mounting mode	Vertical Horizontal
Poles description	4P
[Ue] rated operational voltage	440 V AC
[Ui] rated insulation voltage	750 V AC
[Uimp] rated impulse withstand voltage	8 kV
[Ie] rated operational current	630 A
[In] rated current	630 A at 40 °C
[Icw] rated short-time withstand current	25 kA for 1 s
[Ipk] rated peak withstand current	40 kA
I <sup>2</sup> t on activation	625000000 A <sup>2</sup> .s
Busbar cross section	32 x 8 mm
Connections - terminals	Supply: crimped lug 50 mm <sup>2</sup> Supply: flexible bars, 32 x 8 mm Distribution: M6 holes (phase) , 13 x 1...50 mm <sup>2</sup>
Height	235 mm
Width	470 mm
Depth	115 mm
Net weight	5.6 kg

### Environment

Standards	IEC 61439-2 EN/IEC 61439-1
Product certifications	ASEFA

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.5 cm
Package 1 Width	26 cm
Package 1 Length	55 cm
Package 1 Weight	5.61 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------