



Main

Range	Prisma
Range of product	Prisma P
Product or component type	Cover frame
Range compatibility	Prisma Prisma P cubicle
Provided equipment	Cover frame
Enclosure mounting	Floor-standing
Type of door	Cover frame
IP degree of protection	IP30

Complementary

Installation description	Cubicle - width 650 mm
Door opening angle	120 °
Number of vertical modules [50 mm]	36
Quantity per set	Set of 1
Height	2000 mm
Width	650 mm
Net weight	6.76 kg
Material	Steel
Surface finish	Smooth Matt
Colour	White (RAL 9001)

Environment

IK degree of protection	IK08 conforming to EN/IEC 62262
Standards	IEC 61439-1 IEC 61439-2
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.200 cm
Package 1 Width	67.700 cm
Package 1 Length	202.300 cm
Package 1 Weight	7.000 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	12
Package 2 Height	105.000 cm
Package 2 Width	120.000 cm
Package 2 Length	202.000 cm
Package 2 Weight	87.880 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Halogen content performance	Halogen free plastic parts product