



Main

Range	Mureva
Product or component type	Wander plug
Device short name	Mureva plug
Plug, socket category	Low voltage
Poles description	2P + E
Network type	AC
Outlet standard	Industrial

Complementary

Plug, socket, control station shape	Straight
[In] rated current	32 A
[Ue] rated operational voltage	200...250 V
Network frequency	50/60 Hz
Ground lug clockwise position	6 h
Plug, socket material	Housing: self-extinguishing engineering polymer
Contacts material	Sleeves: brass
Connections - terminals	Fast connection
Cable cross section	2.5...6 mm ²
Cable outer diameter	11.5...21 mm
Cable entry	Cable gland Fair lead
Thread type	Pg 21
Net weight	0.271 kg
Height	152 mm
Width	95 mm
Depth	95 mm
Colour	Grey (RAL 7035)
Voltage colour	Blue

Environment

Standards	IEC 60309-1 IEC 60309-2
IP degree of protection	IP67 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 62262
Fire resistance	850 °C conforming to IEC 60695-2-11
Relative humidity	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
Operating altitude	2000 m
Ambient air temperature for operation	35 °C (86400 s) -25...40 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.3 cm
Package 1 Width	9.4 cm
Package 1 Length	16.9 cm
Package 1 Weight	250 g
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	18 cm
Package 2 Width	26.4 cm
Package 2 Length	27 cm
Package 2 Weight	1.676 kg
Unit Type of Package 3	S03
Number of Units in Package 3	12
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	3.839 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------