Product data sheet
Characteristics

A9C15412
Acti9, step by stel control iATL4

Main

Range of product	Acti9
Device short name	iATL4
Product or component type	Step by stel control auxiliary
[Uc] control circuit voltage	230 V AC 50/60 Hz impulse 50 ms

Complementary

[Ui] rated insulation voltage	440 V
[Uimp] rated impulse withstand voltage	4 kV
Remote control type	Push-button
Step sequences	1st impulse - TL1 on, TL2 off 3rd impulse - TL1 on, TL2 on 4th impulse - TL1 off, TL2 off 2nd impulse - TL1 off, TL2 on
Mounting mode	Fixed, between 2 TL
Mounting support	DIN rail
9 mm pitches	4
Height	86 mm
Width	36 mm
Depth	71 mm
Colour	White
Connections - terminals	Tunnel type terminals0.5…4 mm² - rigid Tunnel type terminals0.5…4 mm² - rigid - with cable end Tunnel type terminals1…4 mm² - flexible Tunnel type terminals1…4 mm² - flexible - with cable end
Wire stripping length	11 mm
Tightening torque	1 N.m
Range compatibility	Acti 9 Acti9 iTL iTL Acti 9 Acti9 iTL iTLi Acti 9 Acti9 iTL iTLs Acti 9 Acti9 iTL iTLc
Product compatibility	ITL (32 A) ITL (16 A)

Environment

Overvoltage category	III
IP degree of protection	IP20 conforming to IEC 60529
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-20…50 °C
Ambient air temperature for storage	-40…70 °C
Standards	EN/IEC 60669-2-2

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.0 cm
Package 1 Width	8.5 cm
Package 1 Length	11.0 cm
Package 1 Weight	200.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	36
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	7.701 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACh Regulation	REACh Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months