Product data sheet
Characteristics

56SB4-GY
Clipsal - 56 Series, Switchboard Enclosure, 4 Module, Surface Mount, Full DIN Rail

Main

Colour	Grey
Range	Clipsal - 56 Series
Range of product	Series 56
Product brand	Clipsal
Product or component type	Distribution board
Device application	Distribution
Colour	Grey (RAL 7035)

Complementary

Device mounting	Surface
Mounting mode	Wall-mounted
Number of modules	4
Cover type	Transparent Hinged cover
Material	Polycarbonate: housing
Height	204 mm
Width	101 mm
Depth	139 mm
Net weight	1.03 kg
Mounting support	DIN rail

Environment

IP degree of protection	IP66
Standards	AS 3100
Ambient air temperature for operation	-25…75 °C
IP degree of protection	IP66 conforming to AS 60529

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.6 cm
Package 1 Width	10.2 cm
Package 1 Length	20.1 cm
Package 1 Weight	945.0 g

Offer Sustainability

REACh Regulation	REACh Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.