

## Product data sheet

### Characteristics

# 31ROFT

Run On timer, Standard Series, Clipsal, 1A, with selectable Turn ON and Turn OFF delays, translucent green

#### Main

|                           |                   |
|---------------------------|-------------------|
| Product or component type | Run on timer      |
| Product brand             | Clipsal           |
| Range of product          | Standard Series   |
| Device presentation       | Mechanism         |
| Colour tint               | Translucent green |
| Range                     | Standard Series   |

#### Complementary

|                                |                   |
|--------------------------------|-------------------|
| Device mounting                | Flush             |
| Material                       | Plastic           |
| Surface finish                 | Glossy            |
| Autonomy                       | 5 minutes         |
| [Ue] rated operational voltage | 230/240 V AC      |
| Network frequency              | 50 Hz             |
| Rated current                  | 1 A               |
| Fixing mode                    | By screws         |
| Main colour tint               | Translucent green |
| Depth                          | 12 mm             |
| Width                          | 41 mm             |
| Height                         | 40 mm             |
| IP degree of protection        | IP30              |
| Net weight                     | 17 g              |

#### Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Height             | 6 cm     |
| Package 1 Width              | 2.6 cm   |
| Package 1 Length             | 5 cm     |
| Package 1 Weight             | 39 g     |
| Unit Type of Package 2       | CAR      |
| Number of Units in Package 2 | 100      |
| Package 2 Height             | 13.3 cm  |
| Package 2 Width              | 26.3 cm  |
| Package 2 Length             | 27.3 cm  |
| Package 2 Weight             | 4.525 kg |
| Unit Type of Package 3       | PAL      |
| Number of Units in Package 3 | 11200    |
| Package 3 Height             | 110 cm   |

|                  |        |
|------------------|--------|
| Package 3 Width  | 114 cm |
| Package 3 Length | 114 cm |
| Package 3 Weight | 517 kg |

### Offer Sustainability

|   |   |
|---|---|
| Packaging without single use plastic                  | No  |
| Packaging made with recycled cardboard                | Yes   |
| REACH Regulation                                      | <a href="#">REACH Declaration</a>             |
| REACH free of SVHC                                    | Yes   |
| EU RoHS Directive                                     | Compliant <a href="#">EU RoHS Declaration</a> |
| RoHS exemption information                            | <a href="#">Yes</a>                           |
| China RoHS Regulation                                 | <a href="#">China RoHS Declaration</a>        |
| Environmental Disclosure                              | <a href="#">Product Environmental Profile</a> |
| Circularity Profile                                   | <a href="#">End Of Life Information</a>       |
| Halogen content performance                           | Halogen free plastic parts product            |
| Take-back   | No  |
| Carbon footprint (kg.eq.CO2 per CR, Total Life cycle) | 16  |

### Contractual warranty

|          |         |
|----------|---------|
| Warranty | 3 years |
|----------|---------|