

Product data sheet

Characteristics

41EPBM-VW

Clipsal Iconic Simple Pushbutton Momentary Switch for ControlLink



Main

Range	Clipsal Iconic
Product or component type	Timer
Device presentation	Mechanism

Complementary

Device mounting	Flush
Actuator	Push-button
Fixing mode	Clip-in
Colour tint	Vivid white
Surface finish	Matt
Connections - terminals	Screw terminals
Type of packing	Box
Sale per indivisible quantity	1
Remote control type	Wiser room application
[Ue] rated operational voltage	220...240 V AC 50 Hz
Operating distance	30 m
Control signal type	ControlLink
Connections - terminals	Screw terminals
Number of terminals	2
Wiring configuration	2-wire
Material	PC (UL94 V-2): top PC MAS056 (UL94 V-2): bottom
Height	22 mm
Width	22 mm
Depth	40 mm
Embedding depth	38 mm
Standards	AS/NZS 60669.2.1

Environment

Ambient air temperature for storage	0...60 °C
Ambient air temperature for operation	0...45 °C
Relative humidity	0...90 %

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	41 g
Package 1 Height	3.9 cm
Package 1 width	6.7 cm
Package 1 Length	8.7 cm
Unit Type of Package 2	PAL
Number of Units in Package 2	1728
Package 2 Weight	90.848 kg
Package 2 Height	150 cm
Package 2 width	114 cm
Package 2 Length	114 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	6
Package 3 Weight	422 g
Package 3 Height	9.8 cm
Package 3 width	13 cm
Package 3 Length	15.6 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information