

Product data sheet

Characteristics

56P210-EO

56 Series Plug - 2 Pin - 10A - 250V



Main

Range	Clipsal - 56 Series
Range of product	Series 56
Product brand	Clipsal
Product or component type	Plug
Device application	Power supply

Complementary

[In] rated current	10 A
Poles description	1P + N
[Ue] rated operational voltage	250 V AC 50 Hz conforming to EN 60309-2
Colour	Orange (RAL 2004)
Material	Plastic
Plug, socket category	Low voltage
Material	Polycarbonate: housing
Outlet standard	Industrial
Connections - terminals	Screw terminal 0.75...1 mm ²
Wire stripping length	35 Mm 10 mm
Contacts material	Pins: brass
Cable entry	Cable gland
Thread type	M20
Plug, socket, control station shape	Straight
Quality labels	RCM
Pin arrangement	D
Service life in hours	4 h
Net weight	0.14 kg
Height	67 mm
Width	67 mm
Depth	112.5 mm
Targeted country	Australia

Environment

Standards	AS/NZS 3112
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	103.0 g
Package 1 Height	7 cm
Package 1 width	6.9 cm
Package 1 Length	10 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	0.582 kg
Package 2 Height	6.8 cm
Package 2 width	12.2 cm
Package 2 Length	27.2 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	75
Package 3 Weight	10.5 kg
Package 3 Height	30.2 cm
Package 3 width	35 cm
Package 3 Length	35 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile