

Product data sheet

Characteristics

56P215/32-EO

Clipsal - 56 Series, Plug Top, Straight, 2 Polarised PIN, 15A, 32V, IP66



Main

Range	Clipsal - 56 Series
Range of product	Series 56
Product brand	Clipsal
Product or component type	Plug
Device application	Power supply

Complementary

[In] rated current	15 A
[Ue] rated operational voltage	32 V DC conforming to EN 60309-2
Colour	Orange (RAL 2004)
Material	Plastic
Plug, socket category	Low voltage
Material	Polycarbonate: housing
Outlet standard	Industrial
Connections - terminals	Screw terminal 1.5 mm ²
Wire stripping length	35 Mm 10 mm
Contacts material	Pins: brass
Cable entry	Cable gland
Thread type	M20
Plug, socket, control station shape	Straight
Quality labels	RCM
Pin arrangement	E
Net weight	0.12 kg
Height	67 mm
Width	67 mm
Depth	112.5 mm
Targeted country	Australia

Environment

Standards	AS/NZS 3112
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	18 cm
Package 1 Length	12 cm
Package 1 Weight	102 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	26.7 cm
Package 2 Width	11.5 cm
Package 2 Length	7 cm
Package 2 Weight	0.586 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	75
Package 3 Height	30.2 cm
Package 3 Width	35 cm
Package 3 Length	35 cm
Package 3 Weight	10.5 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile