

Product data sheet

Characteristics

56P440-EO

Plugs and Extension Sockets, Straight Plugs, IP66, 500V 40A, 4 Round Pins



Main

| | |
|---------------------------|---------------------|
| Range | Clipsal - 56 Series |
| Range of product | Series 56 |
| Product brand | Clipsal |
| Product or component type | Plug |
| Device application | Power supply |

Complementary

| | |
|-------------------------------------|---|
| [In] rated current | 40 A |
| Poles description | 3P + E |
| [Ue] rated operational voltage | 500 V AC 50 Hz conforming to EN 60309-2 |
| Colour | Orange (RAL 2004) |
| Material | Plastic |
| Plug, socket category | Low voltage |
| Material | Polycarbonate: housing |
| Outlet standard | Industrial |
| Connections - terminals | Screw terminal 2.5...25 mm ² |
| Wire stripping length | 50 Mm 20 mm |
| Contacts material | Pins: brass |
| Cable entry | Cable gland |
| Thread type | M40 |
| Plug, socket, control station shape | Straight |
| Pin arrangement | O |
| Duration | 7 h |
| Net weight | 0.4 kg |
| Height | 79 mm |
| Width | 79 mm |
| Depth | 168 mm |
| Targeted country | Australia |

Environment

| | |
|---------------------------------------|-----------------------------|
| Standards | AS/NZS 3123 |
| IP degree of protection | IP66 conforming to AS 60529 |
| Ambient air temperature for operation | -25...75 °C |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 9.1 cm |
| Package 1 Width | 9.0 cm |
| Package 1 Length | 19.5 cm |
| Package 1 Weight | 400.0 g |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |