


Product data sheet

Characteristics

A9N21035

Acti9, comb busbar - 1L+N with Aux - 9 mm pitch - 56 modules - 63A



Main

Range	Acti9
Product or component type	Comb busbar
Mounting mode	Horizontal
Accessory / separate part category	Connection accessory
Lines description	1L + N
Length in 18 mm modules	56

Complementary

Number of ways	37 ways Aux + N + 1 L
Poles configuration for 1 way	1 x 1P + N
Connection pitch	9 mm between phase and neutral
Connector type	Tooth
Distance between way	27 mm
Marking	N L
Insulation	Insulated
Device presentation	Cuttable
[Ie] rated operational current	63 A at 40 °C
[Ue] rated operational voltage	230 V AC Ph/N
[Ui] rated insulation voltage	500 V AC conforming to IEC 61439-2
Mounting location	Top on tunnel type terminals
9 mm pitches	112
Width	1000 mm
Colour	Light grey (RAL 7035)
Range compatibility	Acti 9 (Acti9 C40) Acti 9 (Acti9 C40 Vigi) Acti 9 (Acti9 DT40) Acti 9 (Acti9 DT40 Vigi) Acti 9 (Acti9 iDPN) Acti 9 (Acti9 iDPN Vigi) Acti 9 (Acti9 ID C40) Acti 9 (Acti9 IDc) Acti 9 (Acti9 ITG40) Multi9 (Multi9 N40)

Environment

Standards	IEC 60947-7-1 IEC 61439-2
Fire resistance	960 °C (30 s) conforming to IEC 60695-2-1
Pollution degree	3 conforming to IEC 60947-7-1
IP degree of protection	IP20 with end-pieces and tooth covers

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.000 cm
Package 1 Width	12.000 cm
Package 1 Length	101.000 cm
Package 1 Weight	595.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	6.000 cm
Package 2 Width	101.000 cm
Package 2 Length	12.000 cm
Package 2 Weight	2.978 kg
Unit Type of Package 3	P12
Number of Units in Package 3	80
Package 3 Height	112.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	59.648 kg

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------