

## Product data sheet

### Characteristics

# A9XPH324

## Acti9 - comb busbar - 3L - 18 mm pitch - 24 modules - 100A



### Main

Range	Acti9
Product or component type	Comb busbar
Mounting mode	Horizontal
Accessory / separate part category	Connection accessory
Lines description	3L
Length in 18 mm modules	24

### Complementary

Number of ways	8 ways 3 L
Poles configuration for 1 way	1 x 3P
Connection pitch	18 mm
Connector type	Tooth
Distance between way	54 mm
Marking	L1 L2 L3
Insulation	Insulated
Device presentation	Cuttable
[Ie] rated operational current	100 A at 40 °C
[Ue] rated operational voltage	415 V AC
[Ui] rated insulation voltage	500 V AC conforming to IEC 61439-2
Mounting location	Top or bottom on tunnel type terminals Top or bottom on double terminal
9 mm pitches	48
Width	430 mm
Colour	White (RAL 9003)
Range compatibility	Acti 9 (Acti9 iC60) Acti 9 (Acti9 iK60) Acti 9 (Acti9 iID) Acti 9 (Acti9 iID K) Acti 9 (Acti9 iSW) Acti 9 (Acti9 iSW-NA) Multi 9 (Multi9 C60)

### Environment

Standards	IEC 60947-7-1 IEC 61439-2
Fire resistance	960 °C ( 30 s ) conforming to IEC 60695-2-1
Pollution degree	3 conforming to IEC 60947-7-1
IP degree of protection	IP20 with end-pieces and tooth covers

## Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	1.5 cm
Package 1 Length	43 cm
Package 1 Weight	232 g
Unit Type of Package 2	Gyári csomagolás
Number of Units in Package 2	5
Package 2 Height	6 cm
Package 2 Width	8.7 cm
Package 2 Length	46.6 cm
Package 2 Weight	1.278 kg
Unit Type of Package 3	S04
Number of Units in Package 3	40
Package 3 Height	30 cm
Package 3 Width	40 cm
Package 3 Length	60 cm
Package 3 Weight	11 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------