

## Product data sheet

### Characteristics

# A9A26963

undervoltage release, Acti9, iMNs, voltage release, 220...240 V AC



### Main

Range of product	Acti 9
Product or component type	Undervoltage release
Device short name	IMNs
[Uc] control circuit voltage	220...240 V AC 50/60 Hz
Control type	Delayed
9 mm pitches	2

### Complementary

Range compatibility	Acti 9 iC65 Acti 9 ARA Acti 9 iDPN Vigi Acti 9 iID Acti 9 iSW-NA Acti 9 RCA Acti 9 iDPN (China version) Acti 9 iC60 double terminals miniature circuit breaker Acti 9 iC40
Local signalling	Action indicator
Mounting mode	Clip-on
Mounting support	DIN rail
Width	18 mm
Colour	White
Connections - terminals	Clamp terminal - 1 cable(s) 10 mm <sup>2</sup> - rigid Clamp terminal - 2 cable(s) 2.9 mm <sup>2</sup> - rigid Clamp terminal - 1 cable(s) 8 mm <sup>2</sup> - flexible Clamp terminal - 2 cable(s) 2.9 mm <sup>2</sup> - flexible with cable end
Tightening torque	1 N.m
Compatibility code	IMNs

### Environment

Standards	EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-40...85 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	81 g
Package 1 Height	3 cm
Package 1 width	8 cm

Package 1 Length	9.4 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Weight	710 g
Package 2 Height	9 cm
Package 2 width	26.5 cm
Package 2 Length	10 cm
Unit Type of Package 3	S03
Number of Units in Package 3	72
Package 3 Weight	6.882 kg
Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------