



Main

Range of product	Acti 9
Device short name	IATL4
Product or component type	Step by stel control auxiliary
[Uc] control circuit voltage	230 V AC 50/60 Hz impulse 50 ms

Complementary

[Ui] rated insulation voltage	440 V
[Uimp] rated impulse withstand voltage	4 kV
Remote control type	Push-button
Step sequences	1st impulse - TL1 on, TL2 off 3rd impulse - TL1 on, TL2 on 4th impulse - TL1 off, TL2 off 2nd impulse - TL1 off, TL2 on
Mounting mode	Fixed, between 2 TL
Mounting support	DIN rail
9 mm pitches	4
Height	86 mm
Width	36 mm
Depth	71 mm
Colour	White
Connections - terminals	Tunnel type terminals 0.5...4 mm ² - rigid Tunnel type terminals 0.5...4 mm ² - rigid - with cable end Tunnel type terminals 1...4 mm ² - flexible Tunnel type terminals 1...4 mm ² - flexible - with cable end
Wire stripping length	11 mm
Tightening torque	1 N.m
Range compatibility	Acti 9 iTL iTL Acti 9 iTL iTLi Acti 9 iTL iTLs Acti 9 iTL iTLc
Product compatibility	ITL (32 A) ITL (16 A)

Environment

Overvoltage category	III
IP degree of protection	IP20 conforming to IEC 60529
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-20...50 °C
Ambient air temperature for storage	-40...70 °C
Standards	EN/IEC 60669-2-2

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	200 g
Package 1 Height	6 cm
Package 1 width	8.5 cm
Package 1 Length	11 cm
Unit Type of Package 2	S03
Number of Units in Package 2	36
Package 2 Weight	7.701 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------