

## Product data sheet

### Characteristics

# A9C15413

## Acti 9 control by illuminated push-buttons iATLz



### Main

Range of product	Acti 9
Device short name	IATLz
Product or component type	Impedance adaptation auxiliary
[Uc] control circuit voltage	130...240 V AC 50/60 Hz

### Complementary

[Ui] rated insulation voltage	440 V
[Uimp] rated impulse withstand voltage	4 kV
Remote control type	Illuminated push-button 3 mA
Mounting mode	Fixed, on left side of TL
Mounting support	DIN rail
9 mm pitches	2
Height	86 mm
Width	18 mm
Depth	71 mm
Colour	White
Connections - terminals	Tunnel type terminals 0.5...4 mm <sup>2</sup> - rigid Tunnel type terminals 0.5...4 mm <sup>2</sup> - rigid - with cable end Tunnel type terminals 1...4 mm <sup>2</sup> - flexible Tunnel type terminals 1...4 mm <sup>2</sup> - flexible - with cable end
Wire stripping length	11 mm
Tightening torque	1 N.m
Range compatibility	Acti 9 iTL iTL Acti 9 iTL iTLi Acti 9 iTL iTLs Acti 9 iTL iTLc
Product compatibility	ITL (32 A) ITL (16 A)

### Environment

Overvoltage category	III
IP degree of protection	IP20 conforming to IEC 60529
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-20...50 °C
Ambient air temperature for storage	-40...70 °C
Standards	EN/IEC 60669-2-2

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	94 g
Package 1 Height	1.8 cm
Package 1 width	8 cm
Package 1 Length	9 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Weight	1.17 kg
Package 2 Height	9 cm
Package 2 width	9 cm
Package 2 Length	23 cm
Unit Type of Package 3	S03
Number of Units in Package 3	72
Package 3 Weight	7.568 kg
Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free plastic parts product

## Contractual warranty

Warranty	18 months
----------	-----------