


Product data sheet

Characteristics

KDP20ABG4

FEED UNIT 20A LEFT MOUNTING



Main

| | |
|--------------------------------|------------------|
| Range of product | Canalis |
| Product or component type | Feed unit |
| BAR MATERIAL | Aluminium |
| Product compatibility | KDP |
| [Ie] rated operational current | 20 A |
| Mounting location | Left Right |
| Colour | White (RAL 9001) |

Complementary

| | |
|--------------------------------|--|
| Protection type | Without protection |
| [Ue] rated operational voltage | 230...400 V |
| Connections - terminals | Terminal block - Pg 16 - screw clamp connector for 4 mm ² |
| Control type | Without |
| Provided equipment | End cover |
| Mounting mode | By clips |
| Mounting support | Busbar |
| Standards | IEC 60439-2 IEC 61439-6 |
| Width | 159 mm |
| Depth | 64 mm |
| Height | 49 mm |
| Net weight | 120 g |

Environment

| | |
|-------------------------|------------------------------|
| IP degree of protection | IP40 conforming to IEC 60529 |
|-------------------------|------------------------------|

Packing Units

| | |
|------------------------------|--------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 192 g |
| Package 1 Height | 6 cm |
| Package 1 width | 13 cm |
| Package 1 Length | 20 cm |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 25 |
| Package 2 Weight | 6.8 kg |
| Package 2 Height | 20 cm |
| Package 2 width | 30 cm |
| Package 2 Length | 40 cm |
| Unit Type of Package 3 | P06 |
| Number of Units in Package 3 | 300 |

| | |
|------------------|---------|
| Package 3 Weight | 90.1 kg |
| Package 3 Height | 77 cm |
| Package 3 width | 80 cm |
| Package 3 Length | 60 cm |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|