

Product data sheet

Characteristics

EVP1CNL32121

EVlink Charging cable 7m 32A 1-Phase T2-T1

IEC EV accessory

Main

| | |
|------------------------------------|-------------------------|
| Range | EVlink |
| Product or component type | Charging cable |
| Accessory / separate part category | Cabling accessory |
| Network number of phases | Single phase |
| Poles description | 1P + N |
| [In] rated current | 32 A |
| [Us] rated supply voltage | 220...240 V AC 50/60 Hz |
| Socket number | 2 |

Complementary

| | |
|------------------------|--|
| Plug type | T1 / silver plated contacts charging station end |
| Connector type | T2 charging station end silver plated contacts T1 vehicle end silver plated contacts |
| Range compatibility | EVlink EVlink parking EVF1 charging station EVlink EVlink parking EVW1 charging station EVlink EVlink parking EVF2 charging station EVlink EVlink parking EVW2 charging station EVlink EVlink Smart Wallbox EVB1 charging station EVlink EVlink Wallbox EVH2 charging station |
| Standards | IEC 62196-1 IEC 62196-2 |
| Product certifications | CE |
| Length | 7 m |
| Net weight | 3 kg |
| Colour | Grey |

Environment


| | |
|---------------------------------------|------------------------------|
| IP degree of protection | IP44 conforming to IEC 60529 |
| IK degree of protection | IK10 conforming to IEC 62262 |
| Ambient air temperature for operation | -30...50 °C |
| Ambient air temperature for storage | -40...80 °C |
| Relative humidity | 5...95 % |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 9.000 cm |
| Package 1 Width | 34.000 cm |
| Package 1 Length | 38.000 cm |
| Package 1 Weight | 3.003 kg |
| Unit Type of Package 2 | S04 |
| Number of Units in Package 2 | 3 |
| Package 2 Height | 30.000 cm |

| | |
|------------------------------|-----------|
| Package 2 Width | 40.000 cm |
| Package 2 Length | 60.000 cm |
| Package 2 Weight | 9.897 kg |
| Unit Type of Package 3 | P06 |
| Number of Units in Package 3 | 12 |
| Package 3 Height | 75.000 cm |
| Package 3 Width | 60.000 cm |
| Package 3 Length | 80.000 cm |
| Package 3 Weight | 39.588 kg |

Offer Sustainability

| | |
|----------------------------|--|
| SCIP Number | 0a787687-ca4b-4982-8684-548a3b52ac76 |
| REACH Regulation |  REACH Declaration |
| EU RoHS Directive | Compliant with Exemptions |
| Mercury free | Yes |
| RoHS exemption information |  Yes |
| China RoHS Regulation |  China RoHS Declaration |